



Click [here](#) for the 3D model.

#### Dimensions

D	24mm MAX
T	24.5mm MAX
H	15mm MAX
LL	3.5mm +/-1mm
S	12mm NOM
S1	20mm NOM
Wire Size	0.8mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	250
Typical Component Weight	15 g

#### General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	0.03 mH (100 kHz)
Current	7 A
Temperature Range	-40/+120°C
DC Resistance	20 mOhms