



Click [here](#) for the 3D model.

Dimensions

D	49mm MAX
H	40mm MAX
LL	15mm +/-2mm
S	35mm
S1	35mm
Wire Size	1.3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	40
Typical Component Weight	170.1 g

General Information

Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 65 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	14 mH (1kHz)
Current	9 A
Temperature Range	-40/+105°C
DC Resistance	53 mOhms