


## SC-10-340

Aliases (UALSC103400000)

Common Mode Chokes - Power, KEMET, SC, Through-Hole, Common Mode, 3,400 uH



General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	48mm MAX
Т	29mm MAX
LL	30mm +/-2mm
S	10mm
S1	22mm
Wire Size	1.4mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	60
Typical Component Weight	105.7 g

Specifications	
Voltage AC	250 VAC
Inductance	3.4 mH
Rated Current	10 A
Temperature Range	-40/+105°C
DC Resistance	32 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/16/2025 © 2006 - 2025 YAGEO