


SC-10-E035J

Aliases (UALSC10E035J00)

Common Mode Chokes - Power, KEMET, SC-J, Through-Hole, Common Mode, 350 uH



General Information	
Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 46 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	25mm MAX
T	16mm MAX
Н	24mm MAX
LL	4mm +/-1.5mm
S	19.5mm NOM
S1	11mm NOM
Wire Size	1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	150
Typical Component Weight	11 g

Specifications	
Voltage AC	250 VAC
Inductance	0.35 mH
Rated Current	10 A
Temperature Range	-40/+120°C
DC Resistance	8 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/08/2025 © 2006 - 2025 YAGEO