



Click [here](#) for the 3D model.

| Dimensions | |
|------------|------------|
| D | 34mm MAX |
| H | 24mm MAX |
| LL | 5mm +/-2mm |
| S | 21mm |
| S1 | 21mm |
| Wire Size | 1.3mm |

| Packaging Specifications | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 150 |
| Typical Component Weight | 42.5 g |

| General Information | |
|---------------------|---|
| Series | SC |
| Style | Through-Hole |
| RoHS | Yes |
| Notes | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous | Temperature Rise Maximum: 45 K. |
| Core | Mn-Zn Ferrite |

| Specifications | |
|-------------------|---------------|
| Voltage AC | 250 VAC |
| Inductance | 2 mH (10 kHz) |
| Current | 10 A |
| Temperature Range | -40/+120°C |
| DC Resistance | 20 mOhms |