



Click [here](#) for the 3D model.

#### Dimensions

D	42mm MAX
T	41mm MAX
H	30mm MAX
LL	5mm +/-2mm
S	17mm NOM
S1	30mm NOM
Wire Size	1.5mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	100
Typical Component Weight	71g

#### General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	1.5 mH (100 kHz)
Current	12 A
Temperature Range	-40/+105°C
DC Resistance	18 mOhms