



Click [here](#) for the 3D model.

General Information

Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	1.2 mH (10 kHz)
Current	15 A
Temperature Range	-40/+120°C
DC Resistance	6.2 mOhms

Dimensions

D	35mm MAX
T	25mm MAX
H	35mm MAX
LL	3.8mm +/-1mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.6mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	180
Typical Component Weight	45.2 g