



Click [here](#) for the 3D model.

### Dimensions

D	36mm MAX
T	25mm MAX
H	35mm MAX
LL	5mm +/-2mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.7mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	45 g

### General Information

Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 56 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	0.95 mH (10 kHz)
Current	18 A
Temperature Range	-40/+120°C
DC Resistance	5.5 mOhms