


SC-20-D010

Aliases (UALSC20D010000)

Common Mode Chokes - Power, KEMET, SC-D, Through-Hole, Common Mode, 0.01 mH



Click [here](#) for the 3D model.

Dimensions

D	34mm MAX
H	23mm MAX
LL	15mm +/-2mm
S	22mm
S1	21mm
Wire Size	1.7mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	33 g

General Information

Series	SC-D
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	10 uH
Current	20 A
Temperature Range	-40/+105°C
DC Resistance	8 mOhms