


## SC-20-E20JH

Aliases (UALSC20E20JH00)

KEMET, SC-JH, AC Line Filters, Common Mode, 2 mH



Click [here](#) for the 3D model.

### Dimensions

D	51mm MAX
H	34mm MAX
LL	5mm +/-2mm
S	26mm NOM
S1	30mm NOM
Wire Size	1.9mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	48
Typical Component Weight	119.4 g

### General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 80 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	2 mH (100 kHz)
Current	20 A
Temperature Range	-40/+120°C
DC Resistance	10 mOhms