



Click [here](#) for the 3D model.

#### Dimensions

|           |             |
|-----------|-------------|
| D         | 37mm MAX    |
| H         | 24mm MAX    |
| LL        | 15mm +/-2mm |
| S         | 22mm        |
| S1        | 21mm        |
| Wire Size | 2.3mm       |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Packaging                | Tray |
| Packaging Quantity       | 200  |
| Typical Component Weight | 34 g |

#### General Information

|               |   |
|---------------|---|
| Series        | SC-D  |
| Style         | Through-Hole                                |
| RoHS          | Yes   |
| Notes         | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous | Temperature Rise Maximum: 40 K.             |
| Core          | Ni-Zn Ferrite                               |

#### Specifications

|                   |            |
|-------------------|------------|
| Voltage AC        | 250 VAC    |
| Inductance        | 10 uH      |
| Current           | 30 A       |
| Temperature Range | -40/+105°C |
| DC Resistance     | 1.8 mOhms  |