



Click [here](#) for the 3D model.

Dimensions	
D	30mm MAX
H	19mm MAX
LL	4mm +/-1mm
S	10mm
S1	20mm
Wire Size	0.75mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	200
Typical Component Weight	31.8 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 86 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	9.45 mH (10 kHz)
Current	4.3 A
Temperature Range	-40/+120°C
DC Resistance	80 mOhms