


[Click here for the 3D model.](#)
**General Information**

Series	SCR
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 62 K.
Core	Mn-Zn Ferrite

**Dimensions**

D	29mm MAX
T	23mm MAX
H	29mm MAX
LL	4mm +/-1mm
S	18mm NOM
S1	16mm NOM
Wire Size	0.8mm

**Specifications**

Voltage AC	250 VAC
Inductance	10 mH
Rated Current	4 A
Temperature Range	-40/+120°C
DC Resistance	65 mOhms

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	240
Typical Component Weight	27 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.