


## SCR25B-150-1R4A024J

Aliases (UALE21R4A024J0)

Common Mode Chokes - Power, KEMET, SCR25, Through-Hole, Common Mode, 2,400 uH



General Information	
Series	SCR25
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 85 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	36mm MAX
Т	26mm MAX
Н	35mm MAX
LL	5mm +/-1mm
S	14mm NOM
S1	18mm NOM
Wire Size	1.4mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	150
Typical Component Weight	48 g

Specifications	
Voltage AC	500 VAC
Inductance	2.4 mH
Rated Current	15 A
Temperature Range	-40/+120°C
DC Resistance	11.5 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/07/2025 © 2006 - 2025 YAGEO