



Click [here](#) for the 3D model.

General Information

Series	SCR-H
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 68 K.
Core	Mn-Zn Ferrite

Dimensions

D	45mm MAX
T	31mm MAX
H	44mm MAX
LL	5mm +/-2mm
S	18mm NOM
S1	22mm NOM
Wire Size	2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	60
Typical Component Weight	87 g

Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	1.4 mH
Rated Current	22.5 A
Temperature Range	-40/+120°C
DC Resistance	5 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.