


SCR31HA-070-1R1A039JH-P

Aliases (UALF41R1A039JH)
Common Mode Chokes - Power, KEMET, SCR-H, Through-Hole, Common Mode, 3,850 uH



General Information	
Series	SCR-H
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 54 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	37.5mm MAX
Т	38.5mm MAX
Н	16.5mm MAX
LL	4mm +/-1mm
S	11mm NOM
S1	34mm NOM
Wire Size	1.1mm

Specifications		
Voltage AC	250 VAC	
Voltage DC	250 VDC	
Inductance	3.85 mH	
Rated Current	7 A	
Temperature Range	-40/+120°C	
DC Resistance	24 mOhms	

Packaging Specifications	
Packaging	Tray
Packaging Quantity	125
Typical Component Weight	37 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO