



Click [here](#) for the 3D model.

Dimensions

D	37.5mm MAX
T	38.5mm MAX
H	16.5mm MAX
LL	4mm +/-1mm
S	11mm NOM
S1	34mm NOM
Wire Size	1.1mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	125
Typical Component Weight	37 g

General Information

Series	SCR-H
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 54 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	3.85 mH
Current	7 A
Temperature Range	-40/+120°C
DC Resistance	24 mOhms