



General Information

Series	SH
Style	Through-Hole
RoHS	Yes
Miscellaneous	For 2 Lines.

Specifications

Voltage DC	150 VDC
Inductance	3.2 uH
Temperature Range	-25/+80°C
DC Resistance	22 mOhms (per Line MAX)

Click [here](#) for the 3D model.

Dimensions

L	12.5mm MAX
W	10mm MAX
H	12mm MAX
LL	4mm +/-1mm
S	10mm +/-0.5mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	3000
Typical Component Weight	1.71 g