



Click [here](#) for the 3D model.

#### General Information

|               |              |
|---------------|--------------|
| Series        | SH           |
| Style         | Through-Hole |
| RoHS          | Yes          |
| Miscellaneous | For 2 Lines. |

#### Dimensions

|    |               |
|----|---------------|
| L  | 12.5mm MAX    |
| W  | 10mm MAX      |
| H  | 12mm MAX      |
| LL | 4mm +/-1mm    |
| S  | 10mm +/-0.5mm |

#### Specifications

|                   |                         |
|-------------------|-------------------------|
| Voltage DC        | 150 VDC                 |
| Inductance        | 15 uH                   |
| Temperature Range | -25/+80°C               |
| DC Resistance     | 40 mOhms (per Line MAX) |

#### Packaging Specifications

|                          |           |
|--------------------------|-----------|
| Packaging                | Bulk, Box |
| Packaging Quantity       | 3000      |
| Typical Component Weight | 1.7 g     |