


 Click [here](#) for the 3D model.

**General Information**

Series SHO

Style Through-Hole

RoHS Yes

**Dimensions**

L 7.5mm MAX

T 5mm MAX

H 7.5mm MAX

LL 4mm +/-2mm

**Specifications**

Voltage DC 50 VDC

Inductance 99 uH

Temperature Range -25/+80°C

DC Resistance 120 mOhms (per Line MAX)

**Packaging Specifications**

Packaging Bulk, Box

Packaging Quantity 6000

Typical Component Weight 370 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.