


SN12P-500

Aliases (UALSN12P500000)

Differential Mode Chokes - Power, KEMET, SN, Through-Hole, Normal Mode, 100 uH



General Information	
Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Fe

Click here for the 3D model.

Dimensions	
D	26mm MAX
Н	13mm MAX
LL	20mm +/-2mm
S	12mm
L2	1.5mm MAX
Wire Size	1mm

Packaging Specifications		
Packaging	Bulk	
Typical Component Weight	19.5 g	

Specifications	
Inductance	100 uH
Rated Current	5 A
Temperature Range	-40/+105°C
DC Resistance	0.04 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/06/2025 © 2006 - 2025 YAGEO