



Click [here](#) for the 3D model.

#### General Information

Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Fe

#### Dimensions

D	35mm MAX
H	20mm MAX
LL	20mm +/-2mm
S	15mm
L2	3mm MAX
Wire Size	1mm

#### Packaging Specifications

Packaging	Bulk
Typical Component Weight	51.4 g

#### Specifications

Inductance	450 uH (0.1 MHz)
Current	5 A
Temperature Range	-40/+105°C
DC Resistance	0.12 mOhms