



Click [here](#) for the 3D model.

Dimensions	
D	30mm MAX
L	20mm NOM
H	42mm MAX
LL	115mm NOM
L2	250mm MAX
Wire Size	UL1015 AWG16

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	250
Typical Component Weight	19 g

General Information	
Series	SNG
Style	Through-Hole
RoHS	Yes
Qualifications	TUV
Notes	Last time buy due: May. 31, 2024.
Core	Mn-Zn Ferrite or Ni-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	80 uH (160 kHz)
Inductance Tolerance	-30/+50%
Temperature Range	-40/+105°C
DC Resistance	10 mOhms