


## SNT-D10

Aliases (UDLSNT0D100000)

Differential Mode Chokes - Signal, KEMET, SNT, Through-Hole, Common Mode, 2,500 nH



General Information	
Series	SNT
Style	Through-Hole
RoHS	Yes

Click here for the 3D model.

Dimensions	
L	9.5mm MAX
W	6mm MAX
Т	6mm MAX
Н	12.7mm MAX
LL	5mm +/-1mm
S	5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	100
Typical Component Weight	1.08 g

Specifications	
Inductance	2.5 uH
Temperature Range	-20/+60°C
DC Resistance	25 mOhms (MAX)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO