




SS11VL-R05350

Aliases (UAL11VLR053500) Common Mode Chokes - Power, KEMET, SS11VL, Through-Hole Bobbin, Common Mode, 0.035 H







General Information	
Series	SS11VL
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
L	22mm +/-1mm
Т	14.5mm +/-1mm
Н	19.5mm +/-1mm
LL	3.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.25mm
F	0.8mm +/-0.1mm

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	600	
Typical Component Weight	10.5 g	

Specifications	
Voltage AC	250 VAC
Inductance	35 mH
Rated Current	500 mA
Temperature Range	-40/+120°C
DC Resistance	1.8 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO