



General Information

| | |
|---------------|--|
| Series | SS17VA/HA |
| Style | Through-Hole Bobbin |
| RoHS | Yes |
| Notes | recommended replacement part SSR10VS-10135. |
| Miscellaneous | Inductance Measurement Condition: 1kHz 1V KC530 or equivalent. |

Dimensions

| | |
|-----------|----------------|
| L | 17mm +/-1mm |
| T | 12mm +/-1mm |
| H | 15.1mm +/-1mm |
| LL | 3.5mm +/-1mm |
| S | 12mm +/-1mm |
| S1 | 8mm +/-1mm |
| Wire Size | 0.37mm |
| F | 0.6mm +/-0.1mm |

Packaging Specifications

| | |
|--------------------------|-----|
| Typical Component Weight | 6 g |
|--------------------------|-----|

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 2.5 mH |
| Rated Current | 1 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 0.38 Ohms |