



Click [here](#) for the 3D model.

Dimensions

L	20.6mm +/-1mm
T	16.8mm +/-1mm
H	24.5mm +/-1mm
S	13mm +/-0.5mm
SI	10mm +/-0.5mm
Wire Size	0.32mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	13.2 g

General Information

Series	SS21V
Style	Through-Hole
RoHS	Yes
Notes	Replacement For SS24V Type And SSI 1 V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	17.9 mH
Current	700 mA
Temperature Range	-40/+120°C
DC Resistance	1.1 Ohms