



**General Information**

Series	SS21V
RoHS	Yes
Notes	Replacement For SS24V Type And SSI 1V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

**Specifications**

Voltage AC	250 VAC
Inductance	6.6 mH
Current	1.3 A
Temperature Range	-40/+120°C
DC Resistance	0.35 Ohms

Click [here](#) for the 3D model.

**Dimensions**

L	20.6mm +/-1mm
T	16.8mm +/-1mm
H	24.5mm +/-1mm
S	13mm +/-0.5mm
SI	10mm +/-0.5mm
Wire Size	0.4mm

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	11.5 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.