



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|---------------|
| L | 20.6mm +/-1mm |
| T | 16.8mm +/-1mm |
| H | 24.5mm +/-1mm |
| S | 13mm +/-0.5mm |
| SI | 10mm +/-0.5mm |
| Wire Size | 0.25mm |

Packaging Specifications

| | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 480 |
| Typical Component Weight | 11.6 g |

General Information

| | |
|---------------|---------------------------------|
| Series | SS21VB |
| Style | Through-Hole |
| RoHS | Yes |
| Miscellaneous | Temperature Rise Maximum: 40 K. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 500 VAC |
| Inductance | 25.4 mH |
| Current | 500 mA |
| Temperature Range | -40/+120°C |
| DC Resistance | 1.723 Ohms |