



Click [here](#) for the 3D model.

Dimensions

L	20.6mm +/-1mm
T	16.8mm +/-1mm
H	24.5mm +/-1mm
S	13mm +/-0.5mm
SI	10mm +/-0.5mm
Wire Size	0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	480
Typical Component Weight	11.5 g

General Information

Series	SS21VB
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 35 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Inductance	3.3 mH
Current	1.3 A
Temperature Range	-40/+120°C
DC Resistance	0.226 Ohms