



## SS35V-30082

Aliases (UAL35V30082000, SS35V/H-30082)

Not for New Design

Common Mode Chokes - Power, KEMET, SS35V/35H, Through-Hole Bobbin, Common Mode, 8,200 uH







| Dimensions |               |
|------------|---------------|
| L          | 37mm MAX      |
| Т          | 26.5mm MAX    |
| Н          | 41mm MAX      |
| LL         | 4mm +/-1mm    |
| S          | 21mm +/-0.5mm |
| S1         | 15mm +/-0.5mm |
| F          | 1.2mm NOM     |

| Specifications    |            |
|-------------------|------------|
| Voltage AC        | 250 VAC    |
| Inductance        | 8.2 mH     |
| Rated Current     | 3 A        |
| Temperature Range | -25/+120°C |
| DC Resistance     | 0.15 Ohms  |

## **Packaging Specifications**

Typical Component Weight 59

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO