



General Information

| | |
|---------------|--|
| Series | SS35V/35H |
| Style | Through-Hole Bobbin |
| RoHS | Yes |
| Miscellaneous | Inductance Measurement Condition: 1kHz 1V KC530. |

Dimensions

| | |
|----|---------------|
| L | 37mm MAX |
| T | 26.5mm MAX |
| H | 41mm MAX |
| LL | 4mm +/-1mm |
| S | 21mm +/-0.5mm |
| S1 | 15mm +/-0.5mm |
| F | 1.2mm NOM |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 8.2 mH |
| Rated Current | 3 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 0.15 Ohms |

Packaging Specifications

| | |
|--------------------------|------|
| Typical Component Weight | 59 g |
|--------------------------|------|