


SS35V-35047

Aliases (UAL35V35047000, SS35V/H-35047)

Not for New Design

Common Mode Chokes - Power, KEMET, SS35V/35H, Through-Hole Bobbin, Common Mode, 4,700 uH



General Information	
Series	SS35V/35H
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

 		
Dimensions		
L	37mm MAX	
Т	26.5mm MAX	
Н	41mm MAX	
LL	4mm +/-1mm	
S	21mm +/-0.5mm	

15mm +/-0.5mm

1.2mm NOM

Specifications	
Voltage AC	250 VAC
Inductance	4.7 mH
Rated Current	3.5 A
Temperature Range	-25/+120°C
DC Resistance	0.1 Ohms

Packagin	a Specif	fications
I deltagii	gepeen	

S1

F

Typical Component Weight 57 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/03/2025 © 2006 - 2025 YAGEO