



Click [here](#) for the 3D model.

Dimensions	
L	22mm MAX
T	18mm MAX
H	13.5mm MAX
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	0.32mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	300
Typical Component Weight	9 g

General Information	
Series	SSR10V/H
Style	Through-Hole
Features	Small Standard Common Mode, High Permeability, Compact Size, Low Profile, Light Weight, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	55 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	17 mH (10 kHz)
Current	1A
Temperature Range	-40/+120°C
DC Resistance	0.48 Ohms