



Click [here](#) for the 3D model.

Dimensions

L 22mm MAX

T 18mm MAX

H 13.5mm MAX

LL 3.5mm +/-0.5mm

S 17mm +/-0.5mm

S1 12mm +/-0.5mm

Wire Size 0.23mm

Packaging Specifications

Packaging Tray

Packaging Quantity 300

Typical Component Weight 9 g

General Information

Series SSR10VS/HS

Style Through-Hole

Features Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth

RoHS Yes

Miscellaneous 50 (K) Temperature Rise Max.

Core Mn-Zn Ferrite

Specifications

Voltage AC 250 VAC

Inductance 49.5 mH (10 kHz)

Current 500 mA

Temperature Range -25/+120°C

DC Resistance 1.6 Ohms