



Click [here](#) for the 3D model.

#### General Information

Series	SSR10VS/HS
Features	Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth
RoHS	Yes
Miscellaneous	50 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	18 mH (10 kHz)
Current	800 mA
Temperature Range	-25/+120°C
DC Resistance	0.6 Ohms

#### Dimensions

L	22mm MAX
T	18mm MAX
H	13.5mm MAX
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	0.3mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	9 g