



Click [here](#) for the 3D model.

Dimensions

L 23.5mm MAX

T 13mm MAX

H 21mm MAX

LL 3.5mm +/-0.5mm

S 13mm +/-0.5mm

S1 10mm +/-0.5mm

Wire Size 0.2mm

Packaging Specifications

Packaging Tray

Packaging Quantity 160

Typical Component Weight 9 g

General Information

Series SSR10VS/HS

Style Through-Hole

Features Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth

RoHS Yes

Miscellaneous 50 (K) Temperature Rise Max.

Core Mn-Zn Ferrite

Specifications

Voltage AC 250 VAC

Inductance 74500 uH

Current 400 mA

Temperature Range -25/+120°C

DC Resistance 2.5 Ohms