



Click [here](#) for the 3D model.

Dimensions

L 23.5mm MAX

T 13mm MAX

H 21mm MAX

LL 3.5mm +/-0.5mm

S 13mm +/-0.5mm

S1 10mm +/-0.5mm

Wire Size 0.5mm

Packaging Specifications

Packaging Tray

Packaging Quantity 600

Typical Component Weight 9 g

General Information

Series SSR10VS/HS

Style Through-Hole

Features Compact Size, Low Profile, Light Weight, High Frequency, Broad Bandwidth

RoHS Yes

Miscellaneous 60 (K) Temperature Rise Max.

Core Mn-Zn Ferrite

Specifications

Voltage AC 250 VAC

Inductance 1.3 mH (10 kHz)

Current 3 A

Temperature Range -25/+120°C

DC Resistance 0.06 Ohms