



Click [here](#) for the 3D model.

General Information

Series	SSRH7HS-M
RoHS	Yes
Notes	M07 Lot No.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	15.4 mH (10 kHz)
Current	700 mA
Temperature Range	-40/+120°C
DC Resistance	0.63 Ohms (Per Line)

Dimensions

L	18mm MAX
T	14.5mm MAX
H	12mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
SI	10mm NOM
Wire Size	0.7mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	5.1g