



Click [here](#) for the 3D model.

General Information	
Series	ST
Style	Through-Hole
RoHS	Yes
Miscellaneous	FM Band, Frequency Range: 7 To 100 MHz, Impedance: 600 Ohms (100 MHz).

Dimensions	
L	13mm MAX
T	7mm MAX
H	13mm MAX
LL	10mm +/-2mm
F	0.32mm NOM

Specifications	
Voltage DC	50 VDC
Temperature Range	-20/+75°C
DC Resistance	0.04 Ohms (per Line MAX)

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	6000
Typical Component Weight	1.27 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.