


SU10VFC-R07088

Aliases (UALSU10VR07088)

Common Mode Chokes - Power, KEMET, SU-10VFC-R, Through-Hole Bobbin, Common Mode, 8,800 uH



General Information	
Series	SU-10VFC-R
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

L 18mm MAX T 15.5mm MAX H 15mm MAX	Dimensions	
	L	18mm MAX
H 15mm MAX	Т	15.5mm MAX
	Н	15mm MAX
LL 3.5mm +/-0.7mm	LL	3.5mm +/-0.7mm
S 13mm +/-0.5mm	S	13mm +/-0.5mm
S1 10mm +/-0.5mm	S1	10mm +/-0.5mm
Wire Size 0.25mm	Wire Size	0.25mm
F 0.7mm NOM	F	0.7mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	700
Typical Component Weight	6.3 g

Specifications	
Voltage AC	250 VAC
Inductance	8800 uH
Rated Current	700 mA
Temperature Range	-40/+120°C
DC Resistance	1.1 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/26/2025 © 2006 - 2025 YAGEO