



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|----------------|
| L | 15mm MIN |
| T | 10mm MIN |
| H | 8.5mm MAX |
| LL | 2.3mm +/-0.6mm |
| S | 8mm +/-0.5mm |
| S1 | 7mm +/-0.5mm |
| Wire Size | 0.23mm |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Tray |
| Packaging Quantity | 1800 |
| Typical Component Weight | 1.7 g |

General Information

| | |
|---------------|---------------------------------|
| Series | SU-7VC |
| Style | Through-Hole |
| RoHS | Yes |
| Miscellaneous | Temperature Rise Maximum: 45 K. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 125 VAC |
| Inductance | 350 uH |
| Current | 800 mA |
| Temperature Range | -25/+120°C |
| DC Resistance | 0.22 Ohms |