



General Information

Series	SU-7VC
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	125 VAC
Inductance	250 uH
Current	1.2 A
Temperature Range	-25/+120°C
DC Resistance	0.16 Ohms

Click [here](#) for the 3D model.

Dimensions

L	15mm MIN
T	10mm MIN
H	8.5mm MAX
LL	2.3mm +/-0.6mm
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.25mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	1800
Typical Component Weight	1.7 g