



Click [here](#) for the 3D model.

General Information

Series	SU-9H
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Dimensions

L	17mm MAX
T	15.5mm MAX
H	12.5mm MAX
LL	4mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.1mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3 g

Specifications

Voltage AC	250 VAC
Inductance	18000 uH
Current	100 mA
Temperature Range	-25/+120°C
DC Resistance	8 Ohms