



Click [here](#) for the 3D model.

General Information

Series	SU-9HF
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	6000 uH
Current	300 mA
Temperature Range	-25/+120°C
DC Resistance	2 Ohms

Dimensions

L	17mm MAX
T	15.5mm MAX
H	12mm MAX
LL	3mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.15mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.2 g