



General Information

Series	SU-9V
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	2000 uH
Current	500 mA
Temperature Range	-25/+125°C
DC Resistance	1 Ohms

Click [here](#) for the 3D model.

Dimensions

L	17mm MAX
T	11mm MAX
H	17mm MAX
LL	4mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.5 g