



Click [here](#) for the 3D model.

General Information	
Series	SU-9V
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	500 uH
Rated Current	1 A
Temperature Range	-25/+125°C
DC Resistance	0.3 Ohms

Dimensions	
L	17mm MAX
T	11mm MAX
H	17mm MAX
LL	4mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.27mm
F	0.6mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.4 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.