


USEQMSM1220900

Aliases (USEQMSM1220900)

Not for New Design

KEMET, QMSM, Motion Detection, SMD, Infrared, Small SMD Package, 12C Communication Compatible, High Dynamic Range



General Information	
Series	QMSM
Type	Motion Detection
	SMD
Style	J2
Description	12C Motion Sensor Module
Features	Small SMD Package, 12C Communication Compatible, High Dynamic Range
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	4bbe8810-62a4-426f-9a2e-98d 9d0d9acfe
Qualifications	REACH
MSL	3

Dimensions	
L	13.8mm NOM
L2	10mm NOM
Н	16mm NOM
Packaging Specifications	
Packaging	Bulk
Typical Component Weight	5.4 g

Specifications	
Temperature Range	-40/+85°C
Power Supply Voltage	1.75 - 3.6 V
Current	1-23 uA (Supply Current, Typical)
Miscellaneous	Includes sensor: USEQMSEA220980.
Field of View	60 degrees

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO