



Click [here](#) for the 3D model.

General Information

Series	VM
Type	Varistors
Style	Radial
Description	Contact your local Sales Representative for more information
Features	Through Hole, Dual Function
Termination	Tin
RoHS	With Exemptions
AEC-Q200	No

Specifications

Temperature Range	-40/+125°C
Capacitance	1 uF (1kHz)

Dimensions

Packaging Specifications

Packaging Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.