



Click [here](#) for the 3D model.

General Information

Series	LH
Style	Metal Box
Description	Noise Filters
Features	Three-Phase Terminal Block, High Attenuation Type
RoHS	Yes
Miscellaneous	30 K Self-Temperature Rise Max
Lead	Threaded Studs M6

Dimensions

L	149mm NOM
W	366mm NOM
H	85mm NOM
S	46mm NOM
L1	139mm NOM
L2	129mm NOM
W1	280mm NOM
W2	250mm NOM
Lead	Threaded Studs M6

Packaging Specifications

Specifications

Voltage AC	250 VAC
Voltage AC	250 VAC
Voltage DC	250 VDC
Voltage	250 VDC
Temperature Range	-25/+55C
Leakage Current	1 mA (MAX)
ESR	2000 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.